

PE-Folienbeutel Füll- und Verschließmaschine AVN 442

PE-flim bag filling and closing machine AVN 442



Anwendungsbeschreibung

Die PE-Folienbeutel-Füll und Verschließmaschine AVN 442 befüllt und verpackt stückige food- und nonfood Produkte, die zuvor als Mengeneinheit von einer Wiege- oder Zählmaschine bereitgestellt wurden, sicher in Folienbeutel.

Sie ist lieferbar für Beutel und Tragetaschen mit horizontaler Schweißnaht, aber auch mit KWIK-LOK®, Ultraschall- oder Klebebandverschluss.



Operation description

The PE-film bag filling and closing machine AVN 442 fills and packs solid food such as apples, pears, plums, potatoes, carrots, onions and tomatoes, which have been previously weighed or counted, safely into PE-film bags. The machine is available for bags and carrier bags with a horizontal seam, but also for KWIK-LOK®, ultrasonic or adhesive tape closing units.

The Packaging Innovators



Technische Daten

Leistung:

Bis 1,0 kg: 26 - 28 Beutel / min.

Bis 2,0 kg: 26 - 28 Beutel / min.

Bis 2,5 kg: 26 - 28 Beutel / min.

Bis 3,0 kg: 24 - 26 Beutel / min.

Abmessungen:

L x B x H (in mm): 3.710 x 1.100 x 1.500

Verpackungsmackmaterial:

PE-Folienbeutel auf Rolle, vorgefertigt oder im Halbschlauch

Vorteile der AFFELDT AVN 442:

- Kompakte Abmessungen
- Robustes Design und hohe Zuverlässigkeit
- Einfache Wartung durch große Zugänge
- Einfache Bedienung
- Leicht in vorhandene Systeme zu integrieren
- Vielzahl von Beutelverschließsystem erhältlich

Kombinierbar mit jeder gängigen Wiege- oder Zählmaschine.



Technical data

Capacity:

Up to 1.0 kilos: 26 - 28 bags / min.

Up to 2.0 kilos: 26 - 28 bags / min.

Up to 2.5 kilos: 26 - 28 bags / min.

Up to 3.0 kilos: 24 - 26 bags / min.

Dimensions:

L x W x H (in mm): 3,710 x 1,100 x 1,500

Packaging material:

PE-film bags, Low LD PE-film

Advantages of the AFFELDT AVN 442:

- Compact dimensions
- Solid design and high reliability
- Easy maintenance due to wide access points
- Simple operation
- Easy to integrate in existing systems
- Variety of bag closing systems available

Combination with all dosing machines possible.